UBE + ES/KMK 3 - Marker carriers

1004089

https://www.phoenixcontact.com/us/products/1004089

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker carriers, for the identification of terminal block groups, for E/UK end bracket or E/U end bracket, with 40 x 17 mm perforated insert strip, gray (RAL 7042), unmarked, perforated, mounting type: latching, text field height: 17 mm, text field width: 40 mm

Commercial data

Item number	1004089
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG12
Product key	BG211A
GTIN	4017918011895
Weight per piece (including packing)	6.6 g
Weight per piece (excluding packing)	6.57 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Marker carriers

Dimensions

Width	20.00 mm
Height	42.80 mm
Depth	42.50 mm

Text field

Text field width	40 mm
Text field height	17 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	latching

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.03 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com