PAB-SK 15 - Marker carriers

1013287

https://www.phoenixcontact.com/us/products/1013287

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, unmarked, mounting type: adhesive, text field height: 4 mm, text field width: 15 mm



Your advantages

- Powerful adhesion and optimum grip on standard device surfaces
- Self-adhesive marker carriers for marking devices and components
- These carrier materials can be assemblies with products such as UC-WMT ... and EMT ...

Commercial data

Item number	1013287
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BG12
Product key	BG241A
GTIN	4017918013691
Weight per piece (including packing)	0.368 g
Weight per piece (excluding packing)	0.312 g
Customs tariff number	39269097
Country of origin	SE

Technical data

Product properties

Product type	Marker carriers

Dimensions

Width	9.00 mm
Height	15.00 mm
Depth	3.60 mm

Text field

Text field width	15 mm
Text field height	4 mm

Material specifications

Adhesive strength	500 µm
Adhesive	Acrylic
Color	transparent
Material	PVC
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	80 °C

Mounting

Mounting type	adhesive

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com