FBST 50-PLC RD - Single plug-in bridge

1081050

https://www.phoenixcontact.com/us/products/1081050

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Single plug-in bridge, nominal current: 32 A, length: 50 mm, color: red

Commercial data

Item number	1081050
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	C461
Product key	DK62Z1
GTIN	4055626807812
Weight per piece (including packing)	4.4 g
Weight per piece (excluding packing)	1.6 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Bridge

Electrical properties

Maximum load current	32 A

Connection data

Maximum load current	32 A

Dimensions

Length	50 mm

Material specifications

Color	red (RAL 3001)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (UL (Haz. Loc.))	-40 °C ... 70 °C

Approvals

UL, USA/Canada

Identification	Class I, Zone 2, AEx ec IIC T4
	Class I, Zone 2, Ex ec IIC Gc T4 X

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1081050

cULus Listed
Approval ID: E140324

cULus Listed
Approval ID: E140324

cULus Listed
Approval ID: E140324

cULus Listed
Approval ID: E199827

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.019 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com