# HC-STA-B16-SHWSC-2SSM32-ELC-AL - Housing

1082590

https://www.phoenixcontact.com/us/products/1082590

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surface mounting housing B16, with single locking latch, material: Die-cast aluminum, salt water resistant, protective cover material: PC, cable outlets: 2, lateral, 2x M32, height: 84.7 mm, cable gland: none, protective cover: yes, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

| | |
|---|---|
| Item number | 1082590 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF56 |
| Product key | AF7APB |
| GTIN | 4055626816272 |
| Weight per piece (including packing) | 410 g |
| Weight per piece (excluding packing) | 410 g |
| Customs tariff number | 85389099 |
| Country of origin | CN |

## Technical data


### Notes

| | |
|---|---|
| Notes on the product family | For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K |
| Note on application | compatible with module carrier frames with click-in function |

### Product properties

| | |
|---|---|
| Product type | Housing with locking latch |
| Housing type | Surface mounting housing |
| Application | Standard |
| Type | B16 |
| No. of cable outlets | 2 |
| Type of the screw connection | 2x M32 |
| Protective cover | yes |
| Cable outlet | lateral |
| Pg screw connection | none |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 57 mm |
| Height | 84.7 mm |
| Length | 117.5 mm |
| Hole diameter | 5.5 mm |

### Material specifications

| | |
|---|---|
| Flammability rating according to UL 94 | V0 (Interlock) |
| | V0 (Protective cover) |
| Seal material | NBR, conductive (profile gasket) |
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | uncoated |
| Material, protective cover | PC |
| Locking latch material | PA |

### Mechanical properties

Mechanical data

| | |
|---|---|
| Type of the screw connection | 2x M32 |
| Locking type | Latch |

### Connection data

| | |
|---|---|
| Tightening torque | 2 Nm ... 3 Nm (for M5 mounting screws on the surface-mount housing) |

## Mounting

| | |
|---|---|
| Assembly note | One opening is sealed with a plastic filler plug and can be opened using a screwdriver. |


## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Degree of protection | IP66 (with closed protective cover) |
| | IP67 (when plugged in) |
| Enclosure rating (NEMA) | 4 (UL 50e) |
| | 4X (UL 50e) |
| | 12 (UL 50e) |
| Impact strength | IK08 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

## Drawings

Dimensional drawing




Dimensional drawing

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1082590

**DNV**
Approval ID: TAE000037S

**cUL Recognized**
Approval ID: E255026

**UL Recognized**
Approval ID: E255026

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000437 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com