

1406409
<https://www.phoenixcontact.com/us/products/1406409>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Universal, 4-position, Socket, straight, M12, S-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Packaging available for automated pick and place assembly

Commercial data

Item number	1406409
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAGU
GTIN	4046356804349
Weight per piece (including packing)	4.5 g
Weight per piece (excluding packing)	2.89 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier



1406409

<https://www.phoenixcontact.com/us/products/1406409>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Number of positions	4
Connection profile	3+PE
No. of power contacts	3
Seal present	no
Shielded	no
Coding	S
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	630 V
Nominal current I_N	12 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Universal
----------------------	-----------

Material specifications

Material Contact carrier	PA 4T
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

Connector

SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier



1406409

<https://www.phoenixcontact.com/us/products/1406409>

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	S

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Packaging specifications

Type of packaging	Blister
-------------------	---------


SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier

1406409

<https://www.phoenixcontact.com/us/products/1406409>

Drawings

Schematic diagram



Pin assignment of M12 socket, 4-pos., S-coded, socket side view

SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier



1406409

<https://www.phoenixcontact.com/us/products/1406409>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406409>

 cUL Recognized Approval ID: E468743-20190917				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	600 V	12 A	16	-

 UL Recognized Approval ID: E468743-20190917				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	600 V	12 A	16	-

SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier



1406409

<https://www.phoenixcontact.com/us/products/1406409>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FSS-4CON-L180 THR PE - Contact carrier



1406409

<https://www.phoenixcontact.com/us/products/1406409>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com