CA-00000002S00 - Housing for circular connector

1620541

https://www.phoenixcontact.com/us/products/1620541

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector, front mounting without contact insert, straight, SPEEDCON locking, M23, flat gasket, 4x Ø 3.2, shielded: yes, flange dimensions: 25 mm x 25 mm

Commercial data

Item number	1620541
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEP
GTIN	4046356828857
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	17.479 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Circular connector housing
Series	CA
Application	Signal
Shielded	yes
Thread type	M23

Dimensions

Housing

Flange dimensions	25 mm x 25 mm

Material specifications

Material Housing	GD-Zn

Connector

Type	straight

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Altitude	2000 m

Mounting

Mounting type	Front mounting/square flange (4x Ø 3.2 mm)

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.673 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com