
VS-08-A-RJ/MOD-F-IP67-SET-BU - Panel-mount frame

1652910

https://www.phoenixcontact.com/us/products/1652910

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, with the Freenet system, for round panel cutout, with grommet, without mounting screws, with Freenet RJ45 socket insert, CAT5e, socket on socket

Commercial data

Item number	1652910
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNDA
GTIN	4017918951269
Weight per piece (including packing)	23.8 g
Weight per piece (excluding packing)	6.6 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Panel-mount frame
Application	Modular insert
Type	Version 6
Connection profile	RJ45

Electrical properties


Transmission medium	Copper

Connection data

Connection technology

Connection method	Screw connection

Dimensions

Dimensional drawing	
Width	36 mm
Height	36 mm
Length	53.2 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material, flat gasket	NBR
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP67

Mounting

Mounting type	Front mounting

Drawings

Dimensional drawing



Mounting cutout

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440318

ETIM

ETIM 10.0	EC002597

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	1.021 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com