STZ 2-PCC 4-7,62 GY - Strain relief

1882366

https://www.phoenixcontact.com/us/products/1882366

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 2-position version

Strain relief, for the PCC 4/..-ST and 3-pos. ... 4-pos. MCC 1/..-STZ(F) connector, for snapping into the latching chambers, can be labeled with ZB 6

Commercial data

Item number	1882366
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AA38
Product key	AAHZBJ
GTIN	4017918346720
Weight per piece (including packing)	0.773 g
Weight per piece (excluding packing)	0.709 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Strain relief
Product family	STZ
Number of positions	2
Pitch	7.62 mm

Fitting of components

Partial assembly	No

Dimensions

Width	10 mm
Height	3.4 mm
Length	41.3 mm
Pitch	7.62 mm

Material specifications

Color (Housing)	gray (RAL 7042)

Packaging specifications

Type of packaging	packed in cardboard

Classifications

ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.01 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com