# ME MAX B-22,5 KMGY - Filler plug

2707929

https://www.phoenixcontact.com/us/products/2707929

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, width: 20 mm, height: 21.6 mm, depth: 8.1 mm, color: light gray (similar RAL 7035)

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

| | |
|---|---|
| Item number | 2707929 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC08 |
| Product key | ACHABZ |
| GTIN | 4017918906085 |
| Weight per piece (including packing) | 1.29 g |
| Weight per piece (excluding packing) | 1.34 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| Assembly note | Please observe the application note in the download area. |

### Product properties

| | |
|---|---|
| Product type | Filler plug |
| Housing type | DIN rail housing |
| Housing type | Modular housings |
| Housing series | ME-MAX |
| Product family | ME MAX 22,5.. |
| Ventilation openings present | no |

### Dimensions

| | |
|---|---|
| Width | 20 mm |
| Height | 21.6 mm |
| Depth | 8.1 mm |

### Material specifications

| | |
|---|---|
| Color (Filler plug) | light gray (RAL 7035) |
| Material Filler plug | PA |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |

### Environmental and real-life conditions

#### Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

### Mounting

| | |
|---|---|
| Mounting type | Latching |

### Packaging specifications

| | |
|---|---|
| Outer packaging type | Resealable bag |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2707929

**UL Recognized**
Approval ID: E240868

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com