

EB 80- DIK RD - Insertion bridge

2715953

<https://www.phoenixcontact.com/us/products/2715953>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, pitch: 6.2 mm, number of positions: 80, color: red

Commercial data

Item number	2715953
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918061708
Weight per piece (including packing)	35 g
Weight per piece (excluding packing)	34.2 g
Customs tariff number	85366990
Country of origin	DE

EB 80- DIK RD - Insertion bridge

2715953

<https://www.phoenixcontact.com/us/products/2715953>



Technical data

Product properties

Product type	Insertion bridge
Number of positions	80
Pitch	6.2 mm
Potentials	80

Dimensions

Pitch	6.2 mm
-------	--------

Material specifications

Color	red (RAL 3001)
Material	Cu
Insulating material	PA

Mounting

Mounting type	Screw mounting
---------------	----------------

EB 80- DIK RD - Insertion bridge

2715953

<https://www.phoenixcontact.com/us/products/2715953>



Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EB 80- DIK RD - Insertion bridge



2715953
<https://www.phoenixcontact.com/us/products/2715953>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.314 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com