

EMG 30-SP-10K LIN - Setpoint adjuster



2942124

<https://www.phoenixcontact.com/us/products/2942124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Setpoint value potentiometer, to set setpoints individually, resistance value 10 kΩ



Your advantages

- Voltage reference for setpoint definition in conjunction with potentiometers

Commercial data

Item number	2942124
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	C404
Product key	DK1129
GTIN	4017918080617
Weight per piece (including packing)	53.65 g
Weight per piece (excluding packing)	53.65 g
Customs tariff number	85334010
Country of origin	DE

EMG 30-SP-10K LIN - Setpoint adjuster



2942124

<https://www.phoenixcontact.com/us/products/2942124>

Technical data

Product properties

Product type	Setpoint potentiometer
--------------	------------------------

Input data


Potentiometer

Potentiometer, resistance value	10 k Ω $\pm$ 20 %
Linearity	5 % (of final value)
Potentiometer, current-carrying capacity	0.5 W

Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Dimensions

Dimensional drawing	
Width	30 mm
Height	75 mm
Depth	68 mm

Material specifications

Color	green (RAL 6021)
Housing material	Polycarbonate fiber reinforced PC-F

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
---------------------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

EMG 30-SP-10K LIN - Setpoint adjuster


2942124

<https://www.phoenixcontact.com/us/products/2942124>




Drawings

Dimensional drawing



Circuit diagram



EMG 30-SP-10K LIN - Setpoint adjuster



2942124

<https://www.phoenixcontact.com/us/products/2942124>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2942124>



EAC

Approval ID: RU C-DE.A*30.B.01082

EMG 30-SP-10K LIN - Setpoint adjuster



2942124

<https://www.phoenixcontact.com/us/products/2942124>

Classifications

ECLASS

ECLASS-13.0	27371227
ECLASS-15.0	27371227

ETIM

ETIM 10.0	EC001027
-----------	----------

UNSPSC

UNSPSC 21.0	41113600
-------------	----------

EMG 30-SP-10K LIN - Setpoint adjuster



2942124

<https://www.phoenixcontact.com/us/products/2942124>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	34, 6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	08f70c33-3d86-413d-ba1f-a43c10cbc146

EF3.1 Climate Change

CO2e kg	0.32 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com