EMG 37-H 7,5MM KLAR - Covering hood

2947158

https://www.phoenixcontact.com/us/products/2947158

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm

Commercial data

Item number	2947158
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918082628
Weight per piece (including packing)	6.7 g
Weight per piece (excluding packing)	6.62 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Cover
Housing type	Component housing
Housing series	EMG
Product family	EMG
Number of positions	14
Ventilation openings present	no

Dimensions

Width	37.5 mm
Depth	75 mm
Length	38 mm

Material specifications

Color (Housing)	transparent
Material	PC
Flammability rating according to UL 94	V2

Mounting

Mounting type	Snap in

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 10.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.112 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com