UKH 50 EP - Insertion profile

3009228

https://www.phoenixcontact.com/us/products/3009228

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion profile, color: silver-colored



Product description

Insertion profile for flat conductor connection

Commercial data

Item number	3009228
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918091736
Weight per piece (including packing)	4.97 g
Weight per piece (excluding packing)	4.946 g
Customs tariff number	74198090
Country of origin	CN

Technical data

Product properties

Product type	Mounting material

Material specifications

Color	silver-colored
Material	Metal

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Classifications

ECLASS

ECLASS-13.0	27141192
ECLASS-15.0	27141192

ETIM

ETIM 10.0	EC004592

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com