PZ/4 - Strain relief

3040643

https://www.phoenixcontact.com/us/products/3040643

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Strain relief, width: 19.6 mm, height: 48.7 mm, number of positions: 4, color: black



Your advantages

- The conductor can be fixed using Phoenix Contact cable binders
- Strain relief can be snapped onto the outside of the plug as an option

Commercial data

Item number	3040643
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
GTIN	4017918834432
Weight per piece (including packing)	2.17 g
Weight per piece (excluding packing)	2.13 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Strain relief
Number of positions	4

Dimensions

Width	19.6 mm
Height	48.7 mm

Material specifications

Color	black (RAL 9005)
Material	PA-GF
Flammability rating according to UL 94	V0

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/3040643

EAC
Approval ID: RU C-DE.BL08.B.00644

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.006 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com