HV M6/1-VS 2 - Connection element

3049262

https://www.phoenixcontact.com/us/products/3049262

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection element, depth: 4 mm, width: 15 mm, height: 32 mm, number of positions: 2, color: silver-colored

Commercial data

Item number	3049262
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE49
Product key	BE4Z2X
GTIN	4046356313568
Weight per piece (including packing)	15 g
Weight per piece (excluding packing)	14.38 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Product properties

Product type	Bridge
Number of positions	2

Connection data

Maximum load current	125 A

Dimensions

Width	15 mm
Height	32 mm
Depth	4 mm
Drill hole spacing	18 mm
Hole diameter	6.6 mm

Material specifications

Color	silver-colored
Material	Copper

Mechanical properties

Technical data

Drill hole spacing	18 mm

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com