STG-MTN 1,5-2,5 - Crimp contact

3190506

https://www.phoenixcontact.com/us/products/3190506

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module socket contact, inserted in the PCC or HCC plug housing after crimping the conductor, for 1.5 mm^2 ... 2.5 mm^2 conductors

Commercial data


Item number	3190506
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AA03
Product key	AACCEG
GTIN	4017918093372
Weight per piece (including packing)	0.471 g
Weight per piece (excluding packing)	0.462 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Product properties

Product type	Connector
Product family	MSTBC-MT
Pitch	0 mm

Dimensions


Dimensional drawing	
Pitch	-

Material specifications


Contact surface	Tin Sn
Contact surface material	Tin
Metal surface contact area (top layer)	Tin Sn)

Drawings

Dimensional drawing



Diagram


I [A]
22
20
18
16
14
12
10
8
6
4
2
0
0 10 20 30 40 50 60 70 80 90 100 110 120
ϑ [°C]
STG - MTN 1,5 - 2,5
STG - MTN 0,5 - 1,0

Classifications

ECLASS

ECLASS-13.0	27469090
ECLASS-15.0	27469090

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com