RVT-PA 6 - Fastening clip

3240499

https://www.phoenixcontact.com/us/products/3240499

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 2 ... 8 mm

Commercial data

Item number	3240499
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH34A2
GTIN	4046356520331
Weight per piece (including packing)	0.5 g
Weight per piece (excluding packing)	0.476 g
Customs tariff number	39269097
Country of origin	DE

Technical data


Notes

Note on application	For mounting, use the UNIFOX-PVR P 6 rivet setting tool

Product properties

Product type	Filler plug

Dimensions


Dimensional drawing	
Diameter	6 mm
Hole diameter	6 mm
Min. material thickness	8 mm
Max. material thickness	2 mm

Material specifications

Color	white (RAL 9010)
Material	Nylon

Drawings

Dimensional drawing



Classifications

ECLASS

ECLASS-13.0	27400766
ECLASS-15.0	27400766

ETIM

ETIM 10.0	EC002377

UNSPSC

UNSPSC 21.0	39121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.011 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com