EB 2-25/PT - Insertion bridge

3260157

https://www.phoenixcontact.com/us/products/3260157

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 25 mm, number of positions: 2, nominal current: 150 A, length: 73 mm, color: red



Commercial data

Item number	3260157
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356779111
Weight per piece (including packing)	50.6 g
Weight per piece (excluding packing)	50.6 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Product properties

Product type	Insertion bridge
Number of positions	2
Pitch	25 mm

Electrical properties

Maximum load current	150 A

Connection data

Maximum load current	150 A

Dimensions

Width	47.8 mm
Height	73.3 mm
Depth	28.6 mm
Length	73.3 mm
Pitch	25 mm

Material specifications

Color	red (RAL 3001)
Material	Metal
Flammability rating according to UL 94	V0
Coating	tin-plated
Insulating material	PA

Mounting

Mounting type	Screw mounting

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.906 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com