

FBI 2-12 - Fixed bridge



0200075

<https://www.phoenixcontact.com/us/products/0200075>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fixed bridge, pitch: 12 mm, number of positions: 2, length: 8 mm, color: silver-colored



Commercial data

Item number	0200075
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918253554
Weight per piece (including packing)	8.69 g
Weight per piece (excluding packing)	8.58 g
Customs tariff number	85369095
Country of origin	CN

FBI 2-12 - Fixed bridge



0200075

<https://www.phoenixcontact.com/us/products/0200075>

Technical data

Product properties

Product type	Screw bridge
Number of positions	2
Pitch	12 mm

Dimensions

Width	21.6 mm
Height	7.5 mm
Depth	21.45 mm
Length	7.5 mm
Pitch	12 mm

Material specifications

Color	silver-colored
Material	Copper
Insulating material	PA

Mounting

Mounting type	Screw mounting
---------------	----------------

FBI 2-12 - Fixed bridge



0200075

<https://www.phoenixcontact.com/us/products/0200075>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBI 2-12 - Fixed bridge



0200075

<https://www.phoenixcontact.com/us/products/0200075>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com