

# CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool for processing ferrules according to DIN 46228-4, 0.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>, equipped with pressure lock, magazine, cutting, stripping, twisting, and crimping unit.

## Your advantages

- Robust and durable due to use of resistant plastics and annealed metals
- Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30 % time savings since the process steps required for assembling conductors can be carried out using only one tool
- Visualized process flows directly on the pliers simplify operation

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1200101       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3131        |
| GTIN                                 | 4055626042381 |
| Weight per piece (including packing) | 261.4 g       |
| Weight per piece (excluding packing) | 261 g         |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                    |                                                        |
|--------------------|--------------------------------------------------------|
| Product type       | Crimping tool                                          |
| Compression        | Indent crimp                                           |
| Product property   | Cutting, stripping, twisting, and crimping in one tool |
|                    | Tool-free magazine change for ferrules                 |
|                    | Length stop for stripping                              |
|                    | With pressure lock                                     |
| Min. cross section | 0.5 mm <sup>2</sup>                                    |
| Max. cross section | 2.5 mm <sup>2</sup>                                    |
| AWG min            | 20                                                     |
| AWG max            | 14                                                     |

### Connection data

#### Conductor connection

|                             |                                             |
|-----------------------------|---------------------------------------------|
| Cross section range, metric | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Cross section range AWG     | 20 ... 14                                   |
| Stripping length            | 11 mm                                       |

### Dimensions

|        |         |
|--------|---------|
| Width  | 31.5 mm |
| Height | 100 mm  |
| Length | 180 mm  |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200101>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX 4 IN 1 - Multifunctional tool



1200101  
<https://www.phoenixcontact.com/us/products/1200101>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |
| EF3.1 Climate Change                    |                                                                                     |
| CO2e kg                                 | 31.129 kg CO2e                                                                      |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)