

# CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic pliers, for accommodating dies for a wide range of type of contacts up to 120 mm<sup>2</sup>

## Your advantages

- A mechanical drive system keeps the level of force required to an absolute minimum
- Easily foldable jaw holders mean that the dies can be changed quickly
- Wide variety of available dies

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212318       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH313A        |
| GTIN                                 | 4046356454643 |
| Weight per piece (including packing) | 2,675 g       |
| Weight per piece (excluding packing) | 2,489.9 g     |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                                       |
|------------------|---------------------------------------|
| Product type     | Crimping tool                         |
| Compression      | universal                             |
| Product property | Basic pliers for accommodating dies   |
|                  | Joint head for bulky connector shapes |
|                  | With ratchet mechanism                |
|                  | Two-hand operation                    |
|                  | Unlockable pressure lock              |
|                  | Robust and long-lasting               |

### Connection data

#### Conductor connection

|                             |                                           |
|-----------------------------|-------------------------------------------|
| Cross section range, metric | 6 mm <sup>2</sup> ... 120 mm <sup>2</sup> |
| Cross section range AWG     | 10 ... 4/0                                |

### Dimensions

|        |        |
|--------|--------|
| Width  | 130 mm |
| Height | 65 mm  |
| Length | 430 mm |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212318>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-C120 - Crimping pliers



1212318

<https://www.phoenixcontact.com/us/products/1212318>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-C120 - Crimping pliers



1212318  
<https://www.phoenixcontact.com/us/products/1212318>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |
| EF3.1 Climate Change                    |                                                                                     |
| CO2e kg                                 | 71.299 kg CO2e                                                                      |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)