

HC-EVO-D15-CHWS-PL-BK - Housing



1411338

<https://www.phoenixcontact.com/us/products/1411338>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housings D15, with single locking latch, material: PA 6.6-FR, cable outlets: 1, straight/lateral, height: 60 mm, cable gland: none, Standard

Your advantages

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Low weight
- Lower risk of condensation

Commercial data

Item number	1411338
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APN
GTIN	4046356929103
Weight per piece (including packing)	59.5 g
Weight per piece (excluding packing)	59.5 g
Customs tariff number	85389099
Country of origin	PL

HC-EVO-D15-CHWS-PL-BK - Housing



1411338

<https://www.phoenixcontact.com/us/products/1411338>

Technical data


Notes

General	For contact inserts HC-D15, A10
---------	---------------------------------

Product properties

Product type	Housing with locking latch
Housing type	Coupling housings
Product family	HC-EVO-D
Application	Standard
Type	D15
No. of cable outlets	1
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	30 mm
Height	60 mm
Length	63.5 mm

Material specifications

Flammability rating according to UL 94	V0 (Housing) V0 (Interlock)
Housing material	PA 6.6-FR
Locking latch material	PA

Mechanical properties

Mechanical data

Locking type	Latch
--------------	-------

Mounting

Assembly note	The coupling housing must be supplemented with the EVO screw connection. The EVO screw connection is available in 4 sizes. The EVO screw connection is assembled by hand or using a pipe wrench, for example.
---------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
----------------------	------

HC-EVO-D15-CHWS-PL-BK - Housing



1411338

<https://www.phoenixcontact.com/us/products/1411338>

Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-EVO-D15-CHWS-PL-BK - Housing


1411338

<https://www.phoenixcontact.com/us/products/1411338>



Drawings

Dimensional drawing



Dimensional drawing

HC-EVO-D15-CHWS-PL-BK - Housing



1411338

<https://www.phoenixcontact.com/us/products/1411338>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411338>

DNV

Approval ID: TAE000037S

HC-EVO-D15-CHWS-PL-BK - Housing



1411338

<https://www.phoenixcontact.com/us/products/1411338>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.725 kg CO2e
---------	---------------