

# HC-EVO-B16-SHWSC-2SSM25-PLRBK - Housing



1421382

<https://www.phoenixcontact.com/us/products/1421382>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surface mounting housing B16, with single locking latch, material: PA 6.6-FR, protective cover material: PC, cable outlets: 2, lateral, 2x M25, height: 84 mm, cable gland: none, protective cover: yes, Standard, including 2x reducing adapter

## Your advantages

- Lower costs than metal version
- Low weight
- Lower risk of condensation

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1421382       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF57          |
| Product key                          | AF7APL        |
| GTIN                                 | 4055626264998 |
| Weight per piece (including packing) | 254.7 g       |
| Weight per piece (excluding packing) | 248 g         |
| Customs tariff number                | 85389099      |
| Country of origin                    | PL            |

## Technical data


### Notes

|         |                                                                                    |
|---------|------------------------------------------------------------------------------------|
| General | For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K, HV06-I-PR, HV 6-E...C |
|---------|------------------------------------------------------------------------------------|

### Product properties

|                              |                            |
|------------------------------|----------------------------|
| Product type                 | Housing with locking latch |
| Housing type                 | Surface mounting housing   |
| Product family               | HC-EVO-B                   |
| Application                  | Standard                   |
| Type                         | B16                        |
| No. of cable outlets         | 2                          |
| Type of the screw connection | 2x M25                     |
| Protective cover             | yes                        |
| Cable outlet                 | lateral                    |
| Pg screw connection          | none                       |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 57 mm                                                                                |
| Height              | 84 mm                                                                                |
| Length              | 117 mm                                                                               |
| Hole diameter       | 5.5 mm                                                                               |

### Material specifications

|                                        |                                                         |
|----------------------------------------|---------------------------------------------------------|
| Flammability rating according to UL 94 | V0 (Housing)<br>V0 (Interlock)<br>V0 (Protective cover) |
| Seal material                          | NBR                                                     |
| Housing material                       | PA 6.6-FR                                               |
| Material, protective cover             | PC                                                      |
| Locking latch material                 | PA                                                      |

### Mechanical properties

#### Mechanical data

|                              |        |
|------------------------------|--------|
| Type of the screw connection | 2x M25 |
| Locking type                 | Latch  |

## Connection data

|                   |                                                                     |
|-------------------|---------------------------------------------------------------------|
| Tightening torque | 2 Nm ... 3 Nm (for M5 mounting screws on the surface-mount housing) |
|-------------------|---------------------------------------------------------------------|

## Mounting

|               |                                                                                                         |
|---------------|---------------------------------------------------------------------------------------------------------|
| Assembly note | Two plastic reductions M40 to M25 are provided                                                          |
|               | One of the two openings for the screw connections is sealed but can be broken open using a screwdriver. |


## Environmental and real-life conditions

### Ambient conditions

|                                 |                                                        |
|---------------------------------|--------------------------------------------------------|
| Degree of protection            | IP66 (when plugged in or with locked protective cover) |
| Enclosure rating (NEMA)         | 12 (UL 50e)                                            |
| Impact strength                 | IK08                                                   |
| Ambient temperature (operation) | -40 °C ... 125 °C                                      |

## Drawings

Dimensional drawing



Dimensional drawing

1421382

<https://www.phoenixcontact.com/us/products/1421382>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1421382>

### DNV

Approval ID: TAE000037S



### EAC

Approval ID: RU C-DE.AI30.B.01102



### cUL Recognized

Approval ID: E255026



### UL Recognized

Approval ID: E255026

1421382

<https://www.phoenixcontact.com/us/products/1421382>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)