

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Patch cable, CAT5, assembled, 1.5 m



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2832221       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB11          |
| Product key                          | ABNABG        |
| GTIN                                 | 4046356043960 |
| Weight per piece (including packing) | 67 g          |
| Weight per piece (excluding packing) | 65.7 g        |
| Customs tariff number                | 85444210      |
| Country of origin                    | PL            |

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Product family      | RJ45 STANDARD CAT5      |
| Number of positions | 8                       |

### Interfaces

|                      |                       |
|----------------------|-----------------------|
| Signal type/category | Ethernet CAT5, 1 Gbps |
|----------------------|-----------------------|

### Electrical properties

|                       |                      |
|-----------------------|----------------------|
| Nominal voltage $U_N$ | 150 V <sub>rms</sub> |
| Nominal current $I_N$ | 1.5 A                |
| Transmission speed    | 1 Gbps               |

### Material specifications

|                                        |        |
|----------------------------------------|--------|
| Flammability rating according to UL 94 | V0     |
| Outer sheath, material                 | LSFROH |

### Dimensions

|        |          |
|--------|----------|
| Width  | 13 mm    |
| Height | 6.6 mm   |
| Length | 40.05 mm |

### Connector

#### Connection 1

|                             |                           |
|-----------------------------|---------------------------|
| Type                        | Plug straight RJ45 / IP20 |
| Number of positions         | 8                         |
| Shielded                    | yes                       |
| Insertion/withdrawal cycles | ≥ 750                     |
| Degree of protection        | IP20                      |

#### Connection 2

|      |                    |
|------|--------------------|
| Type | Plug straight RJ45 |
|------|--------------------|

### Cable/line

|                                   |                              |
|-----------------------------------|------------------------------|
| Cable length                      | 1.5 m                        |
| External cable diameter           | 5.50 mm                      |
| Outer sheath, material            | LSFROH                       |
| Single wire, number of litz wires | 8                            |
| Single wire, material             | Cu litz wire                 |
| Shielding                         | SF/UTP                       |
| Halogen-free                      | according to IEC 60754-1     |
| Concentration of fumes            | in accordance with IEC 61034 |

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



|                  |                           |
|------------------|---------------------------|
| Flame resistance | according to IEC 60332-3C |
|------------------|---------------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP20             |
| Ambient temperature (operation) | -10 °C ... 60 °C |

## Standards and regulations

|                        |                              |
|------------------------|------------------------------|
| Flame resistance       | according to IEC 60332-3C    |
| Concentration of fumes | in accordance with IEC 61034 |

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2832221>



**EAC**

Approval ID: 19060508

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002599 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.462 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)