

PRZ - Latching

3040614

<https://www.phoenixcontact.com/us/products/3040614>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, number of positions: 2, length: 64 mm, color: orange

Your advantages

- Can be snapped into the plug housing as an option
- The conductor can be fixed using Phoenix Contact cable binders
- Latching and strain relief in one component

Commercial data

Item number	3040614
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
GTIN	4017918832759
Weight per piece (including packing)	1.48 g
Weight per piece (excluding packing)	1.44 g
Customs tariff number	39269097
Country of origin	PL

PRZ - Latching

3040614

<https://www.phoenixcontact.com/us/products/3040614>



Technical data

Product properties

Product type	Mounting material
Number of positions	2

Dimensions

Width	9.7 mm
Height	63.6 mm
Length	63.6 mm

Material specifications

Color	orange (RAL 2003)
Material	PA-GF

PRZ - Latching



3040614

<https://www.phoenixcontact.com/us/products/3040614>

Classifications

ECLASS

ECLASS-13.0	27141192
ECLASS-15.0	27141192

ETIM

ETIM 10.0	EC004592
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.006 kg CO2e
---------	---------------