

UPR/ 2 - Latching



3045567
<https://www.phoenixcontact.com/us/products/3045567>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, width: 10 mm, height: 39.8 mm, number of positions: 2, color: orange

Your advantages

- Can be used in all plug versions
- Snapped into the outside of the plug housing and hooks onto the terminal block housing when the plug is snapped on

Commercial data

Item number	3045567
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE01
Product key	BE114Z
GTIN	4046356055765
Weight per piece (including packing)	1.214 g
Weight per piece (excluding packing)	1.053 g
Customs tariff number	39269097
Country of origin	PL

UPR/ 2 - Latching



3045567

<https://www.phoenixcontact.com/us/products/3045567>

Technical data

Product properties

Product type	Mounting material
Number of positions	2

Dimensions

Width	10 mm
Height	39.8 mm

Material specifications

Color	orange (RAL 2003)
Material	PA-GF
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	115 °C
Relative insulation material temperature index (Elec., UL 746 B)	65 °C

UPR/ 2 - Latching

3045567

<https://www.phoenixcontact.com/us/products/3045567>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.001 kg CO2e