

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, packed in pairs, depth: 54.5 mm, width: 63 mm, height: 214 mm, color: gray



Your advantages

- Route preassembled cables and wires easily, thanks to the patent-pending swivel joint
- Subsequent wiring is easy, thanks to swivel joint openings that can be operated without tools
- Integrated flanges with strain relief make assembly quick and easy
- Easily plan cable harnesses: the cable length is predefined through the swivel arm
- Mechanical cable protection and bundling, thanks to protective covers that can be attached without tools

Commercial data

Item number	3071410
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE61ZX
GTIN	4055626289168
Weight per piece (including packing)	222 g
Weight per piece (excluding packing)	215.5 g
Customs tariff number	39269097
Country of origin	PL

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	63 mm
Height	214 mm
Depth	54.5 mm

Material specifications

Color	gray (RAL 7042)
Material	PC
Flammability rating according to UL 94	V0
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Classifications

ECLASS

ECLASS-13.0	27182811
ECLASS-15.0	27182811

ETIM

ETIM 10.0	EC002620
-----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.749 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com