


# CD-HF 40X80 BU - Cable duct

3240592

<https://www.phoenixcontact.com/us/products/3240592>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, blue, halogen-free, comprising upper part and mounting base, width: 40 mm, height: 80 mm, length: 2000 mm

## Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240592       |
| Packing unit                         | 16 pc         |
| Minimum order quantity               | 16 pc         |
| Sales key                            | BE74          |
| Product key                          | BE7442        |
| GTIN                                 | 4046356630108 |
| Weight per piece (including packing) | 901 g         |
| Weight per piece (excluding packing) | 808.6 g       |
| Customs tariff number                | 39259020      |
| Country of origin                    | DE            |

# CD-HF 40X80 BU - Cable duct

3240592

<https://www.phoenixcontact.com/us/products/3240592>



## Technical data

### Product properties

|              |             |
|--------------|-------------|
| Product type | Wiring duct |
|--------------|-------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 40 mm   |
| Height | 80 mm   |
| Length | 2000 mm |

### Material specifications

|                                                        |                  |
|--------------------------------------------------------|------------------|
| Color                                                  | blue (RAL 5015)  |
| Material                                               | PC/ABS           |
| Flammability rating according to UL 94                 | V0               |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1, HL 2, HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1, HL 2, HL 3 |
| Components                                             | halogen-free     |

### Cable/line

|              |     |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

### Mechanical properties

|                                        |                                   |
|----------------------------------------|-----------------------------------|
| Usage cross-section                    | 2671 mm <sup>2</sup> (100 %)      |
| Number of cables at 60% filling volume | 96 (2.5 mm <sup>2</sup> Ø 3.4 mm) |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C |
|---------------------------------|------------------|

# CD-HF 40X80 BU - Cable duct



3240592

<https://www.phoenixcontact.com/us/products/3240592>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240592>



**CSA**

Approval ID: 80202282



**VDE approval of drawings**

Approval ID: 40058453

**DNV**

Approval ID: TAE00004VN



**UL Recognized**

Approval ID: E328576

# CD-HF 40X80 BU - Cable duct



3240592

<https://www.phoenixcontact.com/us/products/3240592>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400703 |
| ECLASS-15.0 | 27400703 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000012 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# CD-HF 40X80 BU - Cable duct

3240592

<https://www.phoenixcontact.com/us/products/3240592>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 4.223 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)