

SUBCON 15 HD/M-SH - D-SUB bus connector



5604602

<https://www.phoenixcontact.com/us/products/5604602>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB connector, 15-pos, male connector, two 35° cable entries, universal type for all systems, pin assignment: 1, 2, 3, ..., 14, 15 to screw connection terminal block



Commercial data

Item number	5604602
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN10
Product key	DNC511
GTIN	4046356685214
Weight per piece (including packing)	75 g
Weight per piece (excluding packing)	76.5 g
Customs tariff number	85366990
Country of origin	US

SUBCON 15 HD/M-SH - D-SUB bus connector



5604602

<https://www.phoenixcontact.com/us/products/5604602>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Data plug
Pin assignment	All connections are 1:1 on the screw terminal block

Electrical properties

Nominal voltage U_N	48 V AC/DC
Nominal current I_N	≤ 1 A

Connection data

D-SUB connection

Connection method	High density D-SUB pin strip
-------------------	------------------------------

PCB connection

Connection method	Screw connection
Stripping length	5 mm
Conductor cross-section, rigid min.	0.14 mm ²
Conductor cross-section, rigid max.	1.5 mm ²
Conductor cross-section flexible min.	0.14 mm ²
Conductor cross-section flexible max.	1 mm ²
Single-wire/terminal point, rigid AWG min.	26
Single-wire/terminal point, rigid AWG max.	16
Min. AWG conductor cross-section, flexible	26
Max. AWG conductor cross-section, flexible	18
Tightening torque	0.22 Nm ... 0.25 Nm

Interfaces

Signal	Point-to-point
--------	----------------

Dimensions

Width	16 mm
Height	49.8 mm
Length	61 mm

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Housing material	ABS, metal-plated

Cable/line

SUBCON 15 HD/M-SH - D-SUB bus connector



5604602

<https://www.phoenixcontact.com/us/products/5604602>

External cable diameter	4 mm ... 12.7 mm
-------------------------	------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 50
Fixing screws	4-40 UNC
Tightening torque	0.4 Nm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 75 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C
Altitude	5000 m
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

SUBCON 15 HD/M-SH - D-SUB bus connector



5604602

<https://www.phoenixcontact.com/us/products/5604602>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440322

ETIM

ETIM 10.0	EC001132
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SUBCON 15 HD/M-SH - D-SUB bus connector



5604602

<https://www.phoenixcontact.com/us/products/5604602>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com