

# GPK/SK296X200X0.8 WH/BK - Engraving plate



0826831

<https://www.phoenixcontact.com/us/products/0826831>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Engraving plate, Plate, Mixed color, unmarked, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, mounting type: adhesive, Number of individual labels: 1, text field height: 200 mm, text field width: 296 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0826831       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Product key                          | BG2415        |
| GTIN                                 | 4046356362399 |
| Weight per piece (including packing) | 65.81 g       |
| Weight per piece (excluding packing) | 60.13 g       |
| Country of origin                    | DE            |

# GPK/SK296X200X0.8 WH/BK - Engraving plate



0826831

<https://www.phoenixcontact.com/us/products/0826831>

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                             |   |
|-----------------------------|---|
| Number of individual labels | 1 |
|-----------------------------|---|

### Dimensions

|        |           |
|--------|-----------|
| Width  | 296.00 mm |
| Height | 200.00 mm |
| Depth  | 0.93 mm   |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 296 mm |
| Text field height | 200 mm |

### Material specifications

|                       |                      |
|-----------------------|----------------------|
| Adhesive strength     | 50 µm                |
| Adhesive              | Acrylic              |
| Color                 | multicolored (RAL -) |
|                       | white (RAL 9010)     |
|                       | black (RAL 9005)     |
| Material              | TRANSPLY-ABS         |
| Base element material | TRANSPLY-ABS         |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -20 °C ... 85 °C                                                                |
| Recommended ambient temperature (storage/transport) | 20 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

#### Wipe resistance of inscriptions

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# GPK/SK296X200X0.8 WH/BK - Engraving plate



0826831

<https://www.phoenixcontact.com/us/products/0826831>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# GPK/SK296X200X0.8 WH/BK - Engraving plate



0826831  
<https://www.phoenixcontact.com/us/products/0826831>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)