

CARRIER-EMP (60X30) - Marker carriers



0827454

<https://www.phoenixcontact.com/us/products/0827454>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, black (RAL 9005), unmarked, mounting type: screw, rivet, text field height: 30 mm, text field width: 60 mm



Your advantages

- CARRIER-EMP ... marker carriers are used in conjunction with UC-EMP .../US-EMP ... snap-in labels
- They are used to clearly identify devices and control cabinets
- They can be mounted using screws or rivets

Commercial data

Item number	0827454
Packing unit	30 pc
Minimum order quantity	30 pc
Sales key	BG12
Product key	BG241A
GTIN	4046356444583
Weight per piece (including packing)	4.267 g
Weight per piece (excluding packing)	2.5 g
Customs tariff number	39269097
Country of origin	DE

CARRIER-EMP (60X30) - Marker carriers



0827454

<https://www.phoenixcontact.com/us/products/0827454>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	63.00 mm
Height	32.90 mm
Depth	6.00 mm

Text field

Text field width	60 mm
Text field height	30 mm

Material specifications

Color	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	screw, rivet
---------------	--------------

CARRIER-EMP (60X30) - Marker carriers



0827454

<https://www.phoenixcontact.com/us/products/0827454>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CARRIER-EMP (60X30) - Marker carriers



0827454
<https://www.phoenixcontact.com/us/products/0827454>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com