

GW HART USB MODEM - Cable adapter

1003824

<https://www.phoenixcontact.com/us/products/1003824>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB HART modem cable for communication between a PC and HART devices, cable length: 1 m.

Your advantages

- USB HART modem for commissioning, calibrating, and monitoring HART devices



Commercial data

Item number	1003824
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC322
GTIN	4055626472072
Weight per piece (including packing)	70.6 g
Weight per piece (excluding packing)	67.5 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Programming cable
--------------	-------------------

Electrical properties

Transmission medium	Copper
---------------------	--------

Connection data

PC side

Connection method	USB 2.0 Fullspeed
Notes	serial

Device side

Connection method	Minigrabber
Number of positions	2
Notes	HART FSK

Material specifications

Color (Housing)	black (RAL 9005)
-----------------	------------------

Cable/line

Cable length	1 m
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Max. permissible relative humidity (operation)	≤ 90 % (at 25 °C, non-condensing)

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 55024

Noise emission

Standards/regulations	EN 55032
-----------------------	----------

GW HART USB MODEM - Cable adapter



1003824

<https://www.phoenixcontact.com/us/products/1003824>

Classifications

ECLASS

ECLASS-13.0	19179090
ECLASS-15.0	19179090

ETIM

ETIM 10.0	EC002608
-----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

GW HART USB MODEM - Cable adapter



1003824
<https://www.phoenixcontact.com/us/products/1003824>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	25.391 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com