

HC-COM-HCWS-PL-BK - Protective cover



1079395

<https://www.phoenixcontact.com/us/products/1079395>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover COM, with single locking latch, protective cover material: PA, height: 20.5 mm, seal: no, Standard, for pin inserts

Commercial data

Item number	1079395
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF66
Product key	AF7AZC
GTIN	4055626799216
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	22 g
Customs tariff number	39269097
Country of origin	CN

HC-COM-HCWS-PL-BK - Protective cover



1079395


<https://www.phoenixcontact.com/us/products/1079395>

Technical data

Product properties

Product type	Protective cover
Housing type	Protective cover
Series	HC-COM
Application	Standard
Type	COM
Retaining cord present	yes
Seal present	no

Dimensions

Dimensional drawing	
Width	39 mm
Height	20.5 mm
Length	45.8 mm
Diameter	28 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	V0
Material, protective cover	PA
Locking latch material	PA

Mechanical properties

Mechanical data	
Locking type	Latch

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

HC-COM-HCWS-PL-BK - Protective cover


1079395

<https://www.phoenixcontact.com/us/products/1079395>



Drawings

Dimensional drawing



Dimensional drawing

HC-COM-HCWS-PL-BK - Protective cover



1079395

<https://www.phoenixcontact.com/us/products/1079395>

Classifications

ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

ETIM

ETIM 10.0	EC002314
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-COM-HCWS-PL-BK - Protective cover



1079395

<https://www.phoenixcontact.com/us/products/1079395>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com