

# PAB-SK 30 - Marker carriers



1013290

<https://www.phoenixcontact.com/us/products/1013290>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker carriers, unmarked, mounting type: adhesive, text field height: 4 mm, text field width: 30 mm

## Your advantages

- Powerful adhesion and optimum grip on standard device surfaces
- Self-adhesive marker carriers for marking devices and components
- These carrier materials can be assemblies with products such as UC-WMT ... and EMT ...

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1013290       |
| Packing unit                         | 200 pc        |
| Minimum order quantity               | 200 pc        |
| Sales key                            | BG12          |
| Product key                          | BG241A        |
| GTIN                                 | 4017918013707 |
| Weight per piece (including packing) | 0.736 g       |
| Weight per piece (excluding packing) | 0.614 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | SE            |

# PAB-SK 30 - Marker carriers



1013290

<https://www.phoenixcontact.com/us/products/1013290>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

### Dimensions

|        |          |
|--------|----------|
| Width  | 9.00 mm  |
| Height | 30.00 mm |
| Depth  | 3.60 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 30 mm |
| Text field height | 4 mm  |

### Material specifications

|                       |               |
|-----------------------|---------------|
| Adhesive strength     | 500 µm        |
| Adhesive              | Acrylic       |
| Color                 | transparent   |
| Material              | PVC           |
| Base element material | PVC           |
| Components            | Silicone-free |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 80 °C                                                                |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 96 h                  |
| Temperature for testing | 80 °C                 |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# PAB-SK 30 - Marker carriers



1013290

<https://www.phoenixcontact.com/us/products/1013290>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PAB-SK 30 - Marker carriers



1013290  
<https://www.phoenixcontact.com/us/products/1013290>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)