
CF 500/DIE AI 6 - Crimp insert

1212238

https://www.phoenixcontact.com/us/products/1212238

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for ferrules (A... and AI...) 0.08 mm^2 ... 6 mm^2

Product description

TWIN ferrules 0.5 mm^2 ... 4 mm^2

Commercial data

Item number	1212238
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356449830
Weight per piece (including packing)	81.8 g
Weight per piece (excluding packing)	82.2 g
Customs tariff number	84799070
Country of origin	DE

Technical data

Product properties

Product type	Die
Compression	Trapezoidal crimp
Min. cross section	0.14 mm²
Max. cross section	6 mm²

Connection data

Conductor connection

Cross section range, metric	0.08 mm² ... 6 mm²

Material specifications

Color	silver

Cable/line

External cable diameter	0.5 mm ... 2.9 mm

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212238

EAC
Approval ID: RU C-DE.AI30.B.01549

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 10.0	EC002778

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	19.56 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com