

PAB-KTL 23 - Cable marker carrier



1013957

<https://www.phoenixcontact.com/us/products/1013957>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker carrier, unmarked, horizontal, mounting type: Assembly with cable ties, cable diameter: > 10 mm, text field height: 4 mm, text field width: 23 mm



Your advantages

- Marking collars for marking and bundling conductors
- Can be labeled using UC-WMT ... or US-WMT ... plastic labels or the EMT ... insert strips

Commercial data

Item number	1013957
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BG12
Product key	BG231A
GTIN	4017918014131
Weight per piece (including packing)	0.542 g
Weight per piece (excluding packing)	0.372 g
Customs tariff number	39269097
Country of origin	SE

PAB-KTL 23 - Cable marker carrier



1013957

<https://www.phoenixcontact.com/us/products/1013957>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Marking

Printing direction	horizontal
--------------------	------------

Dimensions

Width	23.3 mm
Height	14.5 mm
Depth	4.35 mm

Text field

Text field width	23 mm
Text field height	4 mm

Material specifications

Color	transparent
Material	PVC
Base element material	PVC
Components	Silicone-free

Cable/line

External cable diameter	> 10.00 mm
-------------------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	80 °C

Mounting

PAB-KTL 23 - Cable marker carrier



1013957

<https://www.phoenixcontact.com/us/products/1013957>

Mounting type	Assembly with cable ties
---------------	--------------------------

PAB-KTL 23 - Cable marker carrier



1013957

<https://www.phoenixcontact.com/us/products/1013957>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PAB-KTL 23 - Cable marker carrier



1013957

<https://www.phoenixcontact.com/us/products/1013957>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com