

# BG/S - Angled brackets



1201086  
<https://www.phoenixcontact.com/us/products/1201086>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Angled brackets with M 6 screw, for fixing DIN rails at an angle of 30°, height: 35.4 mm

## Your advantages

- The BG/S brackets can be used to fix DIN rails at a distance from the mounting surface
- 30° tilt angle

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1201086       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE07          |
| Product key                          | BE7112        |
| GTIN                                 | 4017918017200 |
| Weight per piece (including packing) | 43.1 g        |
| Weight per piece (excluding packing) | 42.279 g      |
| Customs tariff number                | 73269098      |
| Country of origin                    | DE            |

# BG/S - Angled brackets

1201086

<https://www.phoenixcontact.com/us/products/1201086>



## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

### Dimensions

|                     |         |
|---------------------|---------|
| Dimensional drawing |         |
| Width               | 19.7 mm |
| Height              | 87 mm   |
| Depth               | 35.4 mm |
| Length              | 87 mm   |

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Steel          |

### Mounting

|               |        |
|---------------|--------|
| Mounting type | screws |
|---------------|--------|

# BG/S - Angled brackets


1201086

<https://www.phoenixcontact.com/us/products/1201086>



## Drawings

Dimensional drawing



# BG/S - Angled brackets

1201086

<https://www.phoenixcontact.com/us/products/1201086>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27370419 |
| ECLASS-15.0 | 27370419 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001024 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# BG/S - Angled brackets



1201086

<https://www.phoenixcontact.com/us/products/1201086>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.108 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)