

ZAP 100 T - Crimping tool, pneumatic



1203262

<https://www.phoenixcontact.com/us/products/1203262>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pneumatic crimping pliers, as table top version, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 4 - 10 mm²



Your advantages

- These crimping pliers have been specially developed for pre-assembling conductors
- The crimping process is activated by a foot valve
- Two integrated recesses allow quick access to the ferrules

Commercial data

Item number	1203262
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4017918018153
Weight per piece (including packing)	2,939 g
Weight per piece (excluding packing)	2,928.4 g
Customs tariff number	84671900
Country of origin	DE

ZAP 100 T - Crimping tool, pneumatic



1203262

<https://www.phoenixcontact.com/us/products/1203262>

Technical data

Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using a foot pedal
	Several die nests
	Integrated part bins for ferrules
	Die width: 12 mm
	Insertion funnel allows for easy positioning

Electrical properties

Frequency range	0 Hz
-----------------	------

Connection data

Conductor connection

Cross section range, metric	4 mm ² ... 10 mm ²
-----------------------------	--

Dimensions

Width	140 mm
Height	70 mm
Length	200 mm

ZAP 100 T - Crimping tool, pneumatic

1203262

<https://www.phoenixcontact.com/us/products/1203262>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1203262>



EAC

Approval ID: RU C-DE.AI30.B.01549



EAC

Approval ID: 0278662

ZAP 100 T - Crimping tool, pneumatic

1203262

<https://www.phoenixcontact.com/us/products/1203262>



Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 10.0	EC002778
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

ZAP 100 T - Crimping tool, pneumatic



1203262

<https://www.phoenixcontact.com/us/products/1203262>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com