# CRIMPFOX DUO 10 SET - Tool set

1044971

https://www.phoenixcontact.com/us/products/1044971

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, CRIMPFOX DUO 10, AI SORTI BOX RD, AI TWIN SORTI BOX BU, TOOL-KIT STANDARD EMPTY

## Product description

Tool set, equipped

## Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools
- Universal tools sets with WIREFOX 10, CRIMPFOX-DUO tools from TOOL fox
- Ideal for TWIN ferrule
- Rugged and heavy-duty tool bags

## Commercial data

| | |
|---|---|
| Item number | 1044971 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3521 |
| GTIN | 4055626622859 |
| Weight per piece (including packing) | 1,040 g |
| Weight per piece (excluding packing) | 1,056.1 g |
| Customs tariff number | 82060000 |
| Country of origin | SE |

## Set consists of

### CRIMPFOX DUO 10 - Crimping pliers

1031721

https://www.phoenixcontact.com/us/products/1031721



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 $mm^2$, max. cross section: 10 $mm^2$, for TWIN ferrules up to 2 x 4 $mm^2$, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

### WIREFOX 10 - Stripping tool

1212150

https://www.phoenixcontact.com/us/products/1212150



Stripping tool, for cables and conductors from 0.02 - 10 $mm^2$, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 $mm^2$ stranded/1.5 $mm^2$ solid, replaceable stripping blade

## AI SORTI BOX RD - Assortment box

3202960

https://www.phoenixcontact.com/us/products/3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

## AI-TWIN SORTI BOX BU - Assortment box

3202986

https://www.phoenixcontact.com/us/products/3202986



Assortment box, supplied with TWIN ferrules in accordance with DIN 46228-4, 50 pcs. each AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

## TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

https://www.phoenixcontact.com/us/products/1212423



Tool box, unequipped

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Tool set |
| Type of packaging | Bag |
| Compression | Trapezoidal crimp |

### Electrical properties

| | |
|---|---|
| Fuse | DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F |

### Dimensions

| | |
|---|---|
| Width | 65 mm |
| Height | 315 mm |
| Length | 165 mm |

### Material specifications

| | |
|---|---|
| Color | black (RAL 9005) |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1044971

**EAC**
Approval ID: RU x-DE.xx08.B.02974

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21045003 |
| ECLASS-15.0 | 21045003 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000149 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27113200 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 10.209 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com