# CUTFOX-S VDE_DB - Diagonal cutter

1212790

https://www.phoenixcontact.com/us/products/1212790

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested, type of packaging: with holder for sales display (backcard)

## Your advantages

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

## Commercial data

| | |
|---|---|
| Item number | 1212790 |
| Packing unit | 1 pc |
| Minimum order quantity | 6 pc |
| Sales key | BH31 |
| Product key | BH311S |
| GTIN | 4046356994668 |
| Weight per piece (including packing) | 230 g |
| Weight per piece (excluding packing) | 227.9 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Cutting tool |
| Application | Al + Cu + piano wire |

### Dimensions

| | |
|---|---|
| Length | 160 mm |

### Material specifications

| | |
|---|---|
| Color | multicolored (RAL -) |

### Cable/line

| | |
|---|---|
| External cable diameter | 0.2 mm ... 11 mm |

### Standards and regulations

| | |
|---|---|
| Tests | DIN EN 60900 (VDE 0682 PART 201) |
| | DIN ISO 5746 |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212790

**EAC**
Approval ID: RU x-DE.xx08.B.02974

**VDE approval of drawings**
Approval ID: 40052526

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21043711 |
| ECLASS-15.0 | 21043711 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000165 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 2.709 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com