

CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm² ... 10 mm², unlockable pressure lock, lateral entry

Your advantages

- The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held
- These compact crimping pliers have been designed to reduce effort when working

Commercial data

Item number	1212045
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356455732
Weight per piece (including packing)	515 g
Weight per piece (excluding packing)	439.7 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX 10S - Crimping pliers

1212045

<https://www.phoenixcontact.com/us/products/1212045>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

Square crimp

Crimping position 1

Min. cross section

0.14 mm²

Max. cross section

10 mm²

AWG min

25

AWG max

7

Connection data

Conductor connection

Cross section range, metric

0.14 mm² ... 10 mm²

Cross section range AWG

25 ... 7

Dimensions

Length

175 mm

Material specifications

Color

black

CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212045>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

Environmental product compliance

EU RoHS		
	Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC		
	REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change		
	CO2e kg	12.528 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com