# TOOL-KIT SOLAR - Tool set

1212071

https://www.phoenixcontact.com/us/products/1212071

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool case, equipped with: crimping pliers, pressing dies for MC3, MC4 and SOLARLOK connectors, stripping tool for commercially available solar cables, stripping tool for SUNCLIX, VDE cable cutter, VDE screwdriver: PH1, PH2, 0.6x3.5 and 0.8x4.0 slots.

## Product description

Tool set, equipped

## Commercial data

| | |
|---|---|
| Item number | 1212071 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3521 |
| GTIN | 4046356454087 |
| Weight per piece (including packing) | 1,940 g |
| Weight per piece (excluding packing) | 1,570.881 g |
| Customs tariff number | 82060000 |
| Country of origin | SE |

## Set consists of

### CRIMPFOX-M - Crimping pliers

1212072

https://www.phoenixcontact.com/us/products/1212072



Basic pliers, for accommodating dies for a wide range of type of contacts

---

### CRIMPFOX-M SR 6-1/DIE - Crimp insert

1212471

https://www.phoenixcontact.com/us/products/1212471




Die, for MC3 solar connectors, lateral entry, 2.5 ... 6 mm$^2$

---

## CRIMPFOX-M SR 6-2/DIE - Crimp insert

1212472

https://www.phoenixcontact.com/us/products/1212472




Die, for MC4 solar connectors, lateral entry, 2.5 - 6 $mm^2$

## CRIMPFOX-M SR 6-3/DIE - Crimp insert

1212473

https://www.phoenixcontact.com/us/products/1212473




Die, for SOLARLOK solar connectors, lateral entry, 2.5 - 6 $mm^2$

## WIREFOX-D SR 6 - Stripping tool

1212507

https://www.phoenixcontact.com/us/products/1212507



**Stripping tool,** for 2.5 - 6 $mm^2$ solar cables, 8.5 mm stripping length, for MC3, MC4 and SOLARLOK contacts

## WIREFOX-D SR 6-1 - Stripping tool

1212511

https://www.phoenixcontact.com/us/products/1212511



Stripping tool, for standard 2.5, 4, and 6 $mm^2$ solar cables, with 15 mm length stop, for SUNCLIX field connectors

## CUTFOX 16 VDE - Cable-cutting tool

1212126

https://www.phoenixcontact.com/us/products/1212126



**Cable cutter,** precision blade with macro-notching, for copper and aluminum up to 50 $mm^2$, VDE 1000 V AC/1500 V DC tested

## SZK PH1 VDE - Screwdriver

1205150

https://www.phoenixcontact.com/us/products/1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

## SZK PH2 VDE - Screwdriver

1205163

https://www.phoenixcontact.com/us/products/1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

## SF-SL 0,6X3,5-100 S-VDE - Screwdriver

1212587

https://www.phoenixcontact.com/us/products/1212587



Actuation tool, for ST terminal blocks, VDE insulated, with slimmer insulation integrated in the blade, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

## SF-SL 0,8X4,0-100 S-VDE - Screwdriver

1212588

https://www.phoenixcontact.com/us/products/1212588



Actuation tool, for ST terminal blocks, VDE insulated, with slimmer insulation integrated in the blade, also suitable for use as a bladed screwdriver, size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

## TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

https://www.phoenixcontact.com/us/products/1212423



Tool box, unequipped

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Tool set |
| Type of packaging | Bag |

### Dimensions

| | |
|---|---|
| Width | 65 mm |
| Height | 315 mm |
| Length | 165 mm |

### Material specifications

| | |
|---|---|
| Color | black (RAL 9005) |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21045003 |
| ECLASS-15.0 | 21045003 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000149 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27113200 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 14.238 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com