

CRIMPFOX-TC 4 - Crimping pliers



1212113

<https://www.phoenixcontact.com/us/products/1212113>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Your advantages

- Crimping pliers for processing turned contacts
- The integrated positioning tool ensures that the contacts are perfectly aligned in the die
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1212113
Packing unit	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4046356454018
Weight per piece (including packing)	723.3 g
Weight per piece (excluding packing)	723.3 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-TC 4 - Crimping pliers



1212113

<https://www.phoenixcontact.com/us/products/1212113>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	1 mm ²
AWG min	26
AWG max	18

Crimping position 2

Max. cross section	1.5 mm ²
AWG max	16

Crimping position 3

Max. cross section	2.5 mm ²
AWG max	14

Crimping position 4

Max. cross section	4 mm ²
AWG max	12

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 4 mm ²
Cross section range AWG	26 ... 12

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black
Material	Steel

CRIMPFOX-TC 4 - Crimping pliers



1212113

<https://www.phoenixcontact.com/us/products/1212113>

Classifications

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC 4 - Crimping pliers



1212113
<https://www.phoenixcontact.com/us/products/1212113>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com