

HC-CIF-B24-BFFD-FH-AL - DIN rail mounting frame



1404211

<https://www.phoenixcontact.com/us/products/1404211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail mounting frame, design: B24, base frame, material: die-cast aluminum, uncoated, 180° hinged, for top frame HC-CIF-B24-HFFD..., for DIN rails NS 35/7.5

Your advantages

- Stable metal version
- Open base, pre-assembled cable harnesses can be used
- Safe capacitive PE even when connected slightly askew

Commercial data

Item number	1404211
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF60
Product key	AF7AHB
GTIN	4046356680233
Weight per piece (including packing)	173.6 g
Weight per piece (excluding packing)	173.9 g
Customs tariff number	85389099
Country of origin	PL

HC-CIF-B24-BFFD-FH-AL - DIN rail mounting frame



1404211


<https://www.phoenixcontact.com/us/products/1404211>

Technical data

Product properties

Product type	DIN rail mounting frame
Housing type	DIN rail mounting frame
Series	HC-CIF-AL
Type	B24
Protective cover	no
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	56 mm
Height	85 mm
Length	120 mm

Material specifications

Material	Cast aluminum, uncoated
Housing material	Cast aluminum, uncoated

Mechanical properties

Mechanical data

Locking type	Nut
	Pin

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

HC-CIF-B24-BFFD-FH-AL - DIN rail mounting frame




1404211

<https://www.phoenixcontact.com/us/products/1404211>


Drawings

Dimensional drawing



Dimensional drawing top view

Dimensional drawing



Dimensional drawing

HC-CIF-B24-BFFD-FH-AL - DIN rail mounting frame



1404211

<https://www.phoenixcontact.com/us/products/1404211>

Classifications

ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

ETIM

ETIM 10.0	EC002310
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-CIF-B24-BFFD-FH-AL - DIN rail mounting frame



1404211

<https://www.phoenixcontact.com/us/products/1404211>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	27.314 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com