

1424827

<https://www.phoenixcontact.com/us/products/1424827>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B32, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg29, height: 94 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1424827
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	AF7APB
GTIN	4055626382326
Weight per piece (including packing)	434.3 g
Weight per piece (excluding packing)	430 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B32-HHFD-1TTP29-EL-AL - Housing



1424827

<https://www.phoenixcontact.com/us/products/1424827>

Technical data


Notes

Note on application	compatible with module carrier frames with click-in function
---------------------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B32
No. of cable outlets	1
Type of the screw connection	1x Pg29
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	82.2 mm
Height	94 mm
Length	94 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg29
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B32-HHFD-1TTP29-EL-AL - Housing




1424827

<https://www.phoenixcontact.com/us/products/1424827>

Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B32-HHFD-1TTP29-EL-AL - Housing



1424827

<https://www.phoenixcontact.com/us/products/1424827>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424827>

DNV

Approval ID: TAE000037S

HC-STA-B32-HHFD-1TTP29-EL-AL - Housing



1424827

<https://www.phoenixcontact.com/us/products/1424827>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-B32-HHFD-1TTP29-EL-AL - Housing



1424827

<https://www.phoenixcontact.com/us/products/1424827>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com