

VS-PP-19-1HE-16-F - Marshalling panel

1652994

<https://www.phoenixcontact.com/us/products/1652994>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch panel, 19" assembly, IP20, with 16 slots for contact inserts with the Freenet system



19" patch bay, for 16 Freenet inserts

Your advantages

- 16 installation slots per rack unit (RU)
- Grounding concept prepared
- Can be optionally equipped with copper and FO inserts
- For easy cable management

Commercial data

Item number	1652994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLBA
GTIN	4017918969967
Weight per piece (including packing)	618 g
Weight per piece (excluding packing)	582.7 g
Customs tariff number	85366990
Country of origin	PL

VS-PP-19-1HE-16-F - Marshalling panel



1652994

<https://www.phoenixcontact.com/us/products/1652994>

Technical data

Product properties

Product type	Patch panel
Application	Einbauplätze für Kontakteinsätze mit Freenet-System
No. of cable outlets	16
Number of module slots	16
Number of slots	16


Electrical properties

Transmission medium	FO
---------------------	----

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Dimensional drawing	
Width	482.2 mm
Height	43.2 mm
Drill hole distance, horizontal	31.6 mm

Material specifications

Color	light gray RAL 7035
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	PC-GF

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	5 °C ... 55 °C

Mounting

Mounting type	19" rack
---------------	----------


VS-PP-19-1HE-16-F - Marshalling panel

1652994

<https://www.phoenixcontact.com/us/products/1652994>



Drawings



RJ45 patch panel

VS-PP-19-1HE-16-F - Marshalling panel



1652994

<https://www.phoenixcontact.com/us/products/1652994>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

VS-PP-19-1HE-16-F - Marshalling panel



1652994

<https://www.phoenixcontact.com/us/products/1652994>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	12.238 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com