

2202007
<https://www.phoenixcontact.com/us/products/2202007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Base latch for panel mounting, width: 28.8 mm, height: 18.7 mm, depth: 4.15 mm, color: orange (similar RAL 2003)



Your advantages

- Easy, tool-free mounting
- Enables easy panel mounting of housing modules
- Flammability rating HB in accordance with UL 94

Commercial data

Item number	2202007
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC12
Product key	ACHCHC
GTIN	4046356963954
Weight per piece (including packing)	2.98 g
Weight per piece (excluding packing)	1.57 g
Customs tariff number	39269097
Country of origin	IN

Technical data

Product properties

Product type	Base latches
Housing type	DIN rail housing
Housing series	EH
Product family	EH

Dimensions

Width	28.8 mm
Height	18.7 mm
Depth	4.15 mm

Material specifications

Color (Housing)	orange (RAL 2003)
Material Housing	POM
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Snap in
---------------	---------

EH SNAPLOCK SET WALL MOUNT OG - Base latch



2202007

<https://www.phoenixcontact.com/us/products/2202007>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EH SNAPLOCK SET WALL MOUNT OG - Base latch



2202007

<https://www.phoenixcontact.com/us/products/2202007>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com