

IB IL SCN-6 SHIELD - Inline shield connector



2726353

<https://www.phoenixcontact.com/us/products/2726353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline shield connector; green (RAL 6021); type: 6 terminal points, Shield connection; Terminal point numbering: 1.1, 2.1 ... 1.4, 2.4; scope: Connection of one shielded cable

Commercial data

Item number	2726353
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	DR01
Product key	DRI1Z1
GTIN	4017918162894
Weight per piece (including packing)	22.36 g
Weight per piece (excluding packing)	21.04 g
Customs tariff number	85366990
Country of origin	DE

IB IL SCN-6 SHIELD - Inline shield connector



2726353

<https://www.phoenixcontact.com/us/products/2726353>

Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Plug

Area of application

Connection of one shielded cable

Connection data

Conductor cross-section, rigid

0.08 mm² ... 1.5 mm²

Conductor cross-section, flexible

0.08 mm² ... 1.5 mm²

Conductor cross-section AWG

28 ... 16

Stripping length

8 mm

Dimensions

Width

12 mm

Height

130.7 mm

Depth

41 mm

Material specifications

Color

green (RAL 6021)

Characteristics

Design,

6 terminal points

Shield connection

IB IL SCN-6 SHIELD - Inline shield connector



2726353

<https://www.phoenixcontact.com/us/products/2726353>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2726353>



cULus Recognized
Approval ID: E140324

IB IL SCN-6 SHIELD - Inline shield connector



2726353

<https://www.phoenixcontact.com/us/products/2726353>

Classifications

ECLASS

ECLASS-13.0	27242692
ECLASS-15.0	27242692

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL SCN-6 SHIELD - Inline shield connector



2726353

<https://www.phoenixcontact.com/us/products/2726353>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.137 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com