WP-BASE HF 13 - Hose clamp

3240966

https://www.phoenixcontact.com/us/products/3240966

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hose clamp, material: Steel, galvanized, color: black/silver

Commercial data

Item number	3240966
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356710749
Weight per piece (including packing)	6.43 g
Weight per piece (excluding packing)	6.43 g
Customs tariff number	39174000
Country of origin	DE

Technical data

Product properties

Product type	Mounting material

Dimensions

Diameter	13 mm
Hole diameter	4.5 mm

Material specifications

Material	Steel, galvanized
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C

Mounting

Mounting type	Screw mounting

Classifications

ECLASS

ECLASS-15.0	27430315
ECLASS-13.0	27430315

ETIM

ETIM 10.0	EC000799

UNSPSC

UNSPSC 21.0	31162900

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.269 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com