

UM108-SE-A60 - Lateral element

2959748

<https://www.phoenixcontact.com/us/products/2959748>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Side element, without foot, tall version, for 60 mm wide U-shaped cover.



Commercial data

Item number	2959748
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDBA
GTIN	4017918131098
Weight per piece (including packing)	14.71 g
Weight per piece (excluding packing)	14.71 g
Customs tariff number	39269097
Country of origin	PL

UM108-SE-A60 - Lateral element

2959748

<https://www.phoenixcontact.com/us/products/2959748>




Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

Dimensions

Dimensional drawing	
Depth	125 mm

Material specifications

Color (Side element)	green (RAL 6021)
Material Lateral element	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)



UM108-SE-A60 - Lateral element

2959748

<https://www.phoenixcontact.com/us/products/2959748>



Drawings



UM108-SE-A60 - Lateral element

2959748

<https://www.phoenixcontact.com/us/products/2959748>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959748>



UL Recognized

Approval ID: E240868

UM108-SE-A60 - Lateral element



2959748

<https://www.phoenixcontact.com/us/products/2959748>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM108-SE-A60 - Lateral element

2959748

<https://www.phoenixcontact.com/us/products/2959748>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.088 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com